



helm-lgk/dsk-3901

Control for Miranda LGK/DSK-3901

Miranda's additions to the Densité range, the LGK-3901 and DSK-3901, can operate in both HD and SD modes, Both cards offer multiple independent keyers. Helm controls all aspects of these cards via ethernet using the Oxtel protocol.

Typical applications for Helm with LGK-3901/DSK-3901 include Channel Branding downstream of Master Control, Emergency Branding Control, and multi-channel playout control and monitoring. Example panels showing Helm control of LGK-3901 and DSK-3901 are available on our website at www.rascular.com.

Features - Helm can control all aspects of the LGK-3901 and DSK-3901, including:

- All Keyers
- Logo browsing and loading (LGK-3901)
- DSK Load Live
- Dynamic tally monitoring
- Audio voiceovers
- Audio output levels
- Audio voiceover levels
- Audio shuffling
- Integrated Easytext CG, including live text updates
- Integrated GPI outputs
- Integrated audio clip playout
- Integrated on-screen clocks
- Preview output control
- Easytext Crawl control
- Animation Control

Helm LGK-3901 Control Panel



Special controls

LGK-3901 can be used with the following special Helm controls for branding engines:

- Image Browser - For viewing and selection of logo by thumbnail image.
- Image Picker - For viewing and selection of logo by name from a 'drop-down' list
- Image Thumbnail - Displays dynamic thumbnail image of logo currently loaded onto any keying layer

Helm-LGK-3901/Helm-DSK-3901 Technical Information	
Compatibility	All current software versions of LGK-3901 and DSK-3901 are supported, in both SD and HD modes. Helm-LGK-3901 and Helm-DSK-3901 requires Helm software V3.3 or later.
Connection	Helm connects to LGK-3901 and DSK-3901 card via Ethernet TCP/IP networking. Both cards are fitted with Ethernet as standard, no additional options are required.

Ordering information Requires Helm-PC-Designer/Helm-PC to operate see Helm data sheet for relevant application/drivers

Helm-LGK-3901 Helm-LGK-3901 licence
Helm-DSK-3901 Helm-DSK-3901 licence

Rascular Technology Ltd.,

The Oak House,
Whitcott Keysett, Clun,
Craven Arms, Shropshire, SY7 8QE,
United Kingdom
Tel/Fax: +44 1588 640 971
Tel/Fax: +44 1604 715 360 (Sales)

Download a full-feature evaluation copy at www.rascular.com
For pricing and delivery information contact our sales office listed below.

E&OE. The information contained in this document is subject to change without notice.